

BATTERY BCI

Group Numbers, Dimensional Specifications, Polarity & Terminals



BCI	Application	L (in)	W (in)	H (in)	L (mm)	W (mm)	H (mm)	Polarity	Terminals
21	Automotive	8.2	6.8	8.8	208	173	222	L/H-POS	TOP - SAE AUTO
21R	Automotive	8.2	6.8	8.8	208	173	222	R/H-POS	TOP - SAE AUTO
22F	Automotive	9.5	6.9	8.3	240	175	211	R/H-POS	TOP - SAE AUTO
22HF	Automotive	9.4	5.5	8.9	241	175	229	R/H-POS	TOP - SAE AUTO
22NF	Automotive	9.4	5.5	8.9	240	140	227	R/H-POS	TOP - SAE AUTO
24	Automotive	10.3	6.8	8.9	260	173	225	L/H-POS	TOP - SAE AUTO
24F	Automotive	10.3	6.8	8.9	260	173	225	R/H-POS	TOP - SAE AUTO
25	Automotive	9.1	6.9	8.9	230	175	225	L/H-POS	TOP - SAE AUTO
26	Automotive	8.2	6.8	7.8	208	173	197	L/H-POS	TOP - SAE AUTO
26R	Automotive	8.2	6.8	7.8	208	173	197	R/H-POS	TOP - SAE AUTO
26 - 70	Automotive	8.2	6.9	7.8	208	173	197	C-LINE	TOP & SIDE
27	Automotive	12.1	6.8	8.9	306	173	225	L/H-POS	TOP - SAE AUTO
27F	Automotive	12.1	6.8	8.9	306	173	225	R/H-POS	TOP - SAE AUTO
29NF	Automotive	13	5.5	8.9	330	140	227	R/H-POS	TOP - SAE AUTO
33	Automotive	13.3	6.8	9.4	338	173	238	R/H-POS	TOP - SAE AUTO
34	Automotive	10.3	6.8	7.9	260	173	200	L/H-POS	TOP - SAE AUTO
34R	Automotive	10.3	6.8	7.9	260	173	200	R/H-POS	TOP - SAE AUTO
34 - 78	Automotive	10.3	6.8	7.9	260	173	200	C-LINE	TOP & SIDE
35	Automotive	9.1	6.9	8.9	230	175	225	R/H-POS	TOP - SAE AUTO
36R	Automotive	10.4	7.3	8.1	263	183	206	R/H-POS	TOP - SAE AUTO
40R	Automotive	10.9	6.9	6.9	278	175	175	R/H-POS	TOP - SAE AUTO
41	Automotive	11.6	6.9	6.9	293	175	175	R/H-POS	TOP - SAE AUTO
42	Automotive	9.6	6.8	6.8	242	175	175	R/H-POS	TOP - SAE AUTO
43	Automotive	13.1	6.9	8	334	175	205	R/H-POS	TOP - SAE AUTO
45	Automotive	9.5	5.5	9	240	140	227	L/H-POS	TOP - SAE AUTO
46	Automotive	10.8	6.8	9	273	173	229	L/H-POS	TOP - SAE AUTO
47	Automotive	9.7	6.9	7.5	246	175	190	R/H-POS	TOP - SAE AUTO
48	Automotive	12.1	6.9	7.6	278	175	190	R/H-POS	TOP - SAE AUTO
49	Automotive	13.9	6.9	7.6	353	175	190	R/H-POS	TOP - SAE AUTO
50	Automotive	13.5	5	10	343	127	254	L/H-POS	TOP - SAE AUTO
51	Automotive	9.4	5.1	8.8	238	129	223	L/H-POS	TOP - SAE AUTO
51R	Automotive	9.4	5.1	8.8	238	129	223	R/H-POS	TOP - SAE AUTO
52	Automotive	7.3	5.8	8.3	186	147	210	L/H-POS	TOP - SAE AUTO
53	Automotive	13	4.7	8.3	330	119	210	L/H-POS	TOP - SAE AUTO
54	Automotive	7.3	6.1	8.4	186	154	212	R/H-POS	TOP - SAE AUTO
55	Automotive	8.6	6.1	8.4	218	154	212	R/H-POS	TOP - SAE AUTO
56	Automotive	10	6.1	8.4	254	154	212	R/H-POS	TOP - SAE AUTO
57	Automotive	8.1	7.2	6.9	205	183	177	R/H-POS	TOP - SAE AUTO
58	Automotive	10.1	7.2	6.9	255	183	175	L/H-POS	TOP - SAE AUTO
58R	Automotive	10.1	7.2	6.9	255	183	175	R/H-POS	TOP - SAE AUTO

Continued on next page

BCI	Application	L (in)	W (in)	H (in)	L (mm)	W (mm)	H (mm)	Polarity	Terminals
59	Automotive	10.1	7.6	7.8	255	193	196	L/H-POS	TOP - SAE AUTO
60	Automotive	13.1	6.3	8.9	332	160	225	R/H-POS	TOP - SAE AUTO
61	Automotive	7.6	6.4	8.9	192	162	225	R/H-POS	TOP - SAE AUTO
62	Automotive	8.9	6.4	8.9	225	162	225	R/H-POS	TOP - SAE AUTO
63	Automotive	10.2	6.4	8.9	258	162	225	R/H-POS	TOP - SAE AUTO
64	Automotive	11.7	6.4	8.9	296	162	225	R/H-POS	TOP - SAE AUTO
65	Automotive	12.1	7.5	7.6	306	192	192	L/H-POS	TOP - SAE AUTO
66	Automotive	12.1	7.6	7.6	306	192	194	L/H-POS	TOP - SAE AUTO
70	Automotive	8.2	7.1	7.3	208	180	186	L/H-POS	SIDE
75	Automotive	9.1	7.1	7.3	230	180	186	L/H-POS	SIDE
78	Automotive	10.3	7.1	7.3	260	180	186	L/H-POS	SIDE
79	Automotive	12.1	7.1	7.4	307	179	188	L/H-POS	SIDE
85	Automotive	9.1	6.8	8	230	173	203	R/H-POS	TOP - SAE AUTO
86	Automotive	9.1	6.8	8	230	173	203	L/H-POS	TOP - SAE AUTO
90	Automotive	9.5	6.9	6.9	242	175	175	R/H-POS	TOP - SAE AUTO
91	Automotive	11	6.9	6.9	278	175	175	R/H-POS	TOP - SAE AUTO
92	Automotive	12.5	6.9	6.9	315	175	175	R/H-POS	TOP - SAE AUTO
93	Automotive	13.9	6.9	6.9	353	175	175	R/H-POS	TOP - SAE AUTO
94R	Automotive	12.4	6.9	7.5	315	175	190	R/H-POS	TOP - SAE AUTO
95R	Automotive	15.6	6.9	7.5	394	175	190	R/H-POS	TOP - SAE AUTO
96R	Automotive	9.6	6.2	6.9	242	175	175	R/H-POS	TOP - SAE AUTO
97R	Automotive	9.9	6.9	7.5	252	175	190	R/H-POS	TOP - SAE AUTO
98R	Automotive	11.2	6.9	7.5	283	175	190	R/H-POS	TOP - SAE AUTO
99	Automotive	8.2	6.9	6.9	207	175	175	L/H-POS	TOP - SAE AUTO
100	Automotive	10.3	7	7.3	260	179	188	L/H-POS	SIDE
101	Automotive	10.3	7	6.7	260	179	170	L/H-POS	SIDE
121R	Automotive	8.3	7	8.5	208	177	215	R/H-POS	TOP - SAE AUTO
124	Automotive	10.4	6.9	8.4	265	175	214	L/H-POS	TOP - SAE AUTO
124R	Automotive	10.8	7	8.6	262	177	218	R/H-POS	TOP - SAE AUTO
140R	Automotive	8.1	6.9	7.5	207	175	190	R/H-POS	TOP - SAE AUTO
151R	Automotive	7.4	4.9	8.9	188	125	225	R/H-POS	TOP - SAE AUTO
19L	6V Commerical	8.5	7	7.5	216	178	191	OPPOSITE CORNERS	TOP - SAE AUTO
3EE	Commerical	19.3	4.4	8.9	491	111	225	L/H-POS	TOP - SAE AUTO
4DLT	Commerical	20	8.2	7.2	508	208	202	L/H-POS	TOP - SAE AUTO
4D	Commerical	20.75	8.75	9.8	527	222	250	R/H-POS	TOP - SAE AUTO
8D	Commerical	20.75	11.12	9.81	527	283	250	R/H-POS	TOP - SAE AUTO
30H	Commerical	13.5	6.81	9.25	343	173	235	L/H-POS	TOP - SAE AUTO
31A	Commerical	13	6.81	9.43	330	173	240	L/H-POS C-LINE	TOP - SAE AUTO
31T	Commerical	13	6.81	9.43	330	173	240	L/H-POS C-LINE	THREADED STUD
U1	Utility	7.75	5.18	7.31	197	132	186	L/H-POS	NUT & BOLT
U1R	Utility	7.75	5.18	7.31	197	132	186	R/H-POS	NUT & BOLT
GC2	6V Golf Car / Utility	10.37	7.18	10.87	264	183	277	OPPOSITE CORNERS	THREADED STUD
GC8	8V Golf Car / Utility	10.37	7.18	10.87	264	183	277	L/H-POS	THREADED STUD
GC12	12V Golf Car / Utility	12.87	7.18	10.87	327	183	277	L/H-POS	THREADED STUD

